



Zertifikat zu EU-Baumusterprüfbescheinigung VN635 170113

für persönliche Schutzausrüstungen

(Auftrag VN635 170113.1)

Ausgestellt für (Hersteller)


Trust Loyalty & Glory Epoch Network Technology Co., Ltd.

No 39, Jiangpu Road, Suzhou Industrial Park

Suzhou City, Jiangsu Province, China

Aufgrund der eingereichten Unterlagen und der durchgeführten Baumusterprüfung wird bescheinigt, dass die neue Persönliche Schutzausrüstung (PSA)

„Respiratory face mask, Model: M-9520“




den Anforderungen der PSA-Verordnung (EU) 2016/425 in der derzeitigen Fassung sowie den geltenden grundlegenden Gesundheitsschutz- und Sicherheitsanforderungen entspricht und erfüllt daher die Anforderungen an

Atemschutzgeräte — Filtrierende Halbmasken zum Schutz gegen Partikeln

gemäß EN 149:2001+A1:2009 Typ-identische Kennzeichnung FFP2 NR

Sie wird zugeordnet der **PSA-Kategorie III**

Über Eigenschaften der PSA informiert die Verwenderinformation. Diese Baumusterprüfbescheinigung gilt bis Ende August 2021.


Dipl.-HTL-Ing. Marion Pfeiler

ÖTI - Institut für Ökologie, Technik und Innovation GmbH, Notifizierte Stelle Nr. NB 0534

Wien, 04.08.2020

*) nicht harmonisierte Norm

"Certificate" Seite 1 von 1 Seiten
zu EU-Baumusterprüfbescheinigung VN635 170113

ÖTI - Institut für Ökologie, Technik und Innovation GmbH | Spengergasse 20, 1050 Vienna, Austria
tel +43 1 5442543-0 | fax +43 1 5442543-10 | email office@oeti.at | FN 326826b | VAT No. ATU65149029
www.oeti.at

Member of TFSTEX Group

CERTIFICATE

Test Report 3175188/2 of 2


Zhangjiagang Zhiyi Medical Health Products Co., Ltd

Introduction

This report has been prepared by Paul Waller and relates to the activity detailed below:

Job/Registration Details	Client Details
Job number: 3175188/2 of 2	Zhangjiagang Zhiyi Medical Health Products Co., Ltd
Job type: Testing Samples Submitted	Renmin Road
Start Date: 20/04/2020	Leyu Town
Test type: Type	Zhangjiagang city
Sample ID: 10189445	Jiangsu
Registration: CE 727911	215622
Scheme: Negative pressure RPE	China
Protocol: PP123	
Scheme Manager: Nathan Shipley	

The report has been approved for issue by T Wicksey – Senior Test Engineer

Approved For Issue
 Issue Date: 1 May 2020

Objectives

This is an independent test evaluation to only certain clauses or sub-clauses of the agreed specification in accordance with the following test programme:

BSI COVID-19 filtering face piece technical specification, for COVID-19 masks for use by healthcare workers

Product Scope

COVID-19 masks for use by healthcare workers

Report Summary

The samples were received on 20 April 2020 and the testing was started on 20 April 2020.

The samples submitted complied with the requirements of the test work conducted.

Test Samples

Sample ID	ER Number	Description
1 to 19	10189445	Model: ZY-MASK-02 Vertical fold flat mask

Description of Test Samples

Sample Description
COVID-19 masks for use by healthcare workers: Model: ZY-MASK-02 Vertical fold flat mask

Test Requirements

Testing in accordance with BSII COVID-19 filtering face piece technical specification

Technical testing specification for COVID-19 masks for use by healthcare workers

EN 149:2001+A1:2009 Performance requirement	EN 149:2001+A1:2009 Test method clause	Requirement	Assessment
7.7 Practical performance The particle filtering half mask shall undergo practical performance tests under realistic conditions. These general tests serve the purpose of checking the equipment for imperfections that cannot be determined by the tests described elsewhere in this standard. Where practical performance tests show the apparatus has imperfections related to wearer's acceptance, the test house shall provide full details of those parts of the practical performance tests which revealed these imperfections. <i>2 test subjects, masks tested 'As received'</i>	Testing shall be done in accordance with 8.4.	During the tests the particle filtering half mask shall be subjectively assessed by the wearer and after the test, comments on the following shall be recorded: a) head harness comfort; b) security of fastenings; c) field of vision; d) any other comments reported by the wearer on request.	Pass
7.9 Leakage 7.9.1 Total inward leakage <i>5 test subjects, masks tested 'As received'</i>	Testing shall be done in accordance with 8.5.	All samples must achieve All individual exercise results tests shall be not greater than 11 % (for FFP2) and, in addition, all arithmetic means for the total inward leakage shall be not greater than 8 % (for FFP2)	Pass
7.9 Leakage 7.9.2 Penetration of filter material <i>3 test samples masks tested 'As received', for NaCl (Sodium Chloride) and PO (Paraffin oil), 3min test</i>	Testing shall be done in accordance with 8.11	6% for both PO and NaCl	Pass
7.12 Carbon dioxide content of the inhalation air <i>3 test samples, masks tested 'As received'</i>	Testing shall be done in accordance with 8.7.	The carbon dioxide content of the inhalation air (dead space) shall not exceed an average of 1,0 % (by volume).	Pass
7.16 Breathing resistance <i>3 test samples, masks tested 'As received'</i>	Testing shall be done in accordance with 8.9	The breathing resistances shall meet the requirements of; 30l/min – 0.7mbar (inhale) 95l/min – 2.4mbar (inhale) 160l/min – 3.0mbar (exhale) If achieves cl 7.9.2 FFP3 class 30l/min – 1.0mbar (inhale) 95l/min – 3.0mbar (inhale) 160l/min – 3.0mbar (exhale)	Pass
Appendix A - Test Panel Data			
Product Photographs			

Glossary of Terms.

Pass: Complies. Tested by BSI engineers at BSI laboratories

Pass 1: Complies. Witnessed by BSI engineers in manufacturers laboratory.

Pass 2: Complies. Tests carried out by third party lab; results accepted by BSI.

Pass*: Report resulted in uncertainty and states that Compliance is more probable than non-compliance.

Fail: Non-compliance. Product does not meet the requirements of this clause.

Fail*: Report resulted in uncertainty and states that Non-compliance is more probable than compliance.

N/T: Not Tested

N/A: Not Applicable

AR: As Received

TC: Temperature Conditioned

SW: Simulated Wear

FT: Flow Tested

MS: Mechanical strength

MMDF: Manufactures Minimum Design Flow

MMDC: Manufactures Minimum Design Condition

Conditions of Issue.

This Test Report is issued subject to the conditions stated in current issue of 'BSI Terms of Service'. The results contained herein apply only to the particular sample(s) tested and to the specific tests carried out, as detailed in this Test Report. The issuing of this Test Report does not indicate any measure of Approval, Certification, Supervision, Control or Surveillance by BSI of any product. No extract, abridgement or abstraction from a Test Report may be published or used to advertise a product without the written consent of BSI, who reserve the absolute right to agree or reject all or any of the details of any items or publicity for which consent may be sought.

Should you wish to speak with BSI in relation to this report, please contact Customer Services on +44 (0)8450 80 9000.

BSI
Kitemark House
Maylands Avenue
Hemel Hempstead
Hertfordshire
HP2 4SQ



Opinions and Interpretations expressed herein are outside the scope of our UKAS accreditation.

Unless otherwise stated, any results not obtained from testing in a BSI laboratory are outside the scope of our UKAS accreditation.

Test Results.

Testing in accordance with BSI COVID-19 filtering face piece technical specification

BS EN 149:2001 +A1:2009 Technical testing specification for COVID-19 masks for use by healthcare workers

CLAUSE	REQUIREMENTS	ASSESSMENT
--------	--------------	------------

7.7 Practical performance

The particle filtering half mask shall undergo practical performance tests under realistic conditions. These general tests serve the purpose of checking the equipment for imperfections that cannot be determined by the tests described elsewhere in this standard.

Where practical performance tests show the apparatus has imperfections related to wearer's acceptance, the test house shall provide full details of those parts of the practical performance tests which revealed these imperfections.

Test in accordance with clause 8.4 of the standard.

Pass

Testing in accordance with BSI COVID-19 filtering face piece technical specification, for masks for use by healthcare workers

During the tests the particle filtering half mask shall be subjectively assessed by the wearer and after the test, comments on the following shall be recorded:

- a) head harness comfort; b) security of fastenings; c) field of vision; d) any other comments reported by the wearer on request.

Table A: Practical performance

Test candidate	Sample	Comments				Assessment
		Head harness comfort	Security of fastenings	Field of vision	Any other comments	
RF1	1 AR	Fine	Good	Fine	None	Pass
GR1	2 AR	OK	Good	OK	Ear loop adjuster was a little uncomfortable	Pass

7.9 Leakage

7.9.1 Total inward leakage

The laboratory tests shall indicate that the particle filtering half mask can be used by the wearer to protect with high probability against the potential hazard to be expected.

The total inward leakage consists of three components: face seal leakage, exhalation valve leakage (if exhalation valve fitted) and filter penetration.

Test in accordance with clause 8.5 of the standard.

Pass

Testing in accordance with BSI COVID-19 filtering face piece technical specification, for masks for use by healthcare workers

5 test subjects, masks tested 'As received'. All individual exercise results tests shall be not greater than 11 % (for FFP2) and, in addition, all arithmetic means for the total inward leakage shall be not greater than 8 % (for FFP2).

Table B: Clause 7.9.1 - Total inward leakage

Test candidate	Sample	Pre test condition	Inward Leakage (%)						Assessment
			A	B	C	D	E	Average	
			Walking	Walking with head side to side	Walking with head up & down	Walking and talking	Walking		
LM2	3	AR	1.30	1.18	2.21	1.43	1.74	1.57	Pass
AA1	4	AR	4.69	7.75	5.19	2.28	4.21	4.21	Pass
SR1	5	AR	2.61	2.71	2.27	1.61	2.06	2.06	Pass
SI1	6	AR	1.20	1.33	2.11	1.58	1.41	1.52	Pass
MM2	7	AR	1.72	0.80	1.17	0.61	1.24	1.11	Pass

Test Results (Continued)

CLAUSE	REQUIREMENTS	ASSESSMENT
--------	--------------	------------

7.9.2 Penetration of filter material

Testing in accordance with BSI COVID-19 filtering face piece technical specification, for masks for use by healthcare workers
 3 test samples masks tested 'As received', for NaCl (Sodium Chloride) and PO (Paraffin oil), 3 min test. Testing shall be done in accordance with 8.11. 6% limit for both PO and NaCl

Pass

Table C: Clause 8.11 - Sodium Chloride penetration test

Sample number	Pre-test condition	Flow through filter (l/min)	Penetration (%)	
			Limit	Actual
8	AR	95	< 6	0.1240
9	AR			0.0195
10	AR			0.0766

Table D: Clause 8.11 - Paraffin oil penetration test

Sample number	Pre-test condition	Flow through filter (l/min)	Penetration (%)	
			Limit	Actual
11	AR	95	< 6	0.9175
12	AR			0.4045
13	AR			1.8150

7.12 Carbon dioxide content of inhalation air

The carbon dioxide content of the inhalation air (dead space) shall not exceed an average of 1.0% (by volume).

Pass

Test in accordance with clause 8.7 of the standard.

Table E: Clause 8.7 - Carbon Dioxide content of the inhalation air

Sample	Pre-test condition	Dead space CO ₂ (%)	
		Limit	Measured
14	AR	< 1.0	0.45
15	AR		0.45
16	AR		0.50

Test Results (Continued)

CLAUSE	REQUIREMENTS	ASSESSMENT
--------	--------------	------------

7.16
Breathing resistance
Testing in accordance with BSI COVID-19 filtering face piece technical specification, for masks for use by healthcare workers

3 test samples masks tested 'As received'. Test in accordance with clause 8.9 of the standard.

The breathing resistances shall meet the requirements of FFP2;
 30l/min – 0.7mbar (inhale), 95l/min – 2.4mbar (inhale), 160l/min – 3.0mbar (exhale)
 If achieves clause 7.9.2 FFP3 class (<1% penetration);
 30l/min – 1.0mbar (inhale), 95l/min – 3.0mbar (inhale), 160l/min – 3.0mbar (exhale)

Pass

Table F: Clause 8.9 – Breathing resistance. Inhalation resistance at a continuous flow

Sample	Pre-test condition	Continuous flow (l/min)	Inhalation resistance (mbar)	
			Limit	Measured
17	AR	30	< 0.7	0.42
18	AR			0.43
19	AR			0.47
17	AR	95	< 2.4	1.37
18	AR			1.36
19	AR			1.48

Table G: Clause 8.9 – Breathing resistance. Exhalation resistance at a continuous flow, measured in five orientations with the worst case reported

Sample	Pre-test condition	Continuous flow (l/min)	Exhalation resistance (mbar)	
			Limit	Measured
17	AR	160	< 3.0	2.25
18	AR			2.27
19	AR			2.18

Appendix A. – Test Panel Data

Test Candidate	Facial Dimensions (mm)					Sex
	Length of face	Width of face	Face depth	Width of mouth	Head Circumference	
RF1	104	122	121	55	549	Male
AA1	125	144	130	47	581	Male
MM2	119	150	115	53	595	Male
GR1	124	145	126	49	590	Male
SR1	118	133	130	52	585	Male
SI1	121	135	142	48	575	Male
LM2	110	148	125	44	589	Male

Note: All candidates were clean shaven


Product photographs.



Front view



Side View



Inside View

End of Report